

Manufacturer: O-I
Model: Ultra-Loc
ASTM Type: IA

Description:

This is a two-piece plastic/plastic continuously-threaded closure (Figure 1).



Figure 1

The closure is opened by pushing down on the closure and simultaneously turning it counterclockwise (Figures 2).



Figure 2

There are two different sets of instructions on the closure. One set of the manufacturer's instructions on the closure are (Figure 2):

(arrow pointing clockwise) CLOSE TIGHTLY (arrow pointing clockwise)

Protect Your Children!

(picture of hand signaling stop with two children's faces)

(arrow pointing counterclockwise) TO OPEN PUSH DOWN & TURN (arrow pointing counterclockwise)

Another example of the instructions are (Figure 3):



Figure 3

(arrow pointing clockwise) CLOSE TIGHTLY (arrow pointing clockwise)

(arrow pointing counterclockwise) TO OPEN PUSH DOWN & TURN (arrow pointing counterclockwise)

Please note that Direct Mail Rx is a fictitious firm and the name was supplied for illustrative purposes.