

Manufacturer: Polyseal Corporation, (a subsidiary of Berry Plastics Corporation)
Model: Lite-Touch
ASTM Type: ID

Description:

This is a one-piece plastic continuously-threaded closure and an o-ring with a tab that fits onto the container neck finish (see red o-ring with a tab in Figure 1).



Figure 1

This closure can be used on a bottle with a dropper nozzle (Figure 2A), a continuous-threaded bottle (Figure 2B), or a tube (Figure 2C).



Figure 2A



Figure 2B



Figure 2C

The package is opened by pushing the red tab to the left, which prevents the red o-ring from moving, while simultaneously turning the closure counterclockwise. On the interior of the closure on the bottom below the continuous threads, there are small vertical lines for 360° and matching small vertical lines on 180° of the red o-ring (Figure 3).



Figure 3

The small vertical lines on the closure interior and o-ring fit together and move as one when the closure is turned to keep the package closed.

The manufacturer's instructions on one dropper nozzle bottle are (Figure 4):



Figure 4

With one hand, push red tab
left with thumb while
unscrewing cap with free hand