

Manufacturer: Van Blarcom Closures Inc.
Model: Saf-Cap IIIA
ASTM Type: IA

Description:

This is a two-piece plastic/plastic-continuously threaded closure. The difference between the Saf-Cap IIIA and the Saf-Cap III is the skirt height. The Saf-Cap IIIA has a higher skirt height than the Saf-Cap III (Figure 1).



Figure 1

There are two versions of this closure. One version has a retention ring to accommodate a lining material on the interior of the closure (see closure in the middle in Figure 2). The second version has a post molded into the interior of the closure, which may accommodate an applicator such as a brush (see closure on the right in Figure 2).



Figure 2

The closure is opened by pushing down on the closure and simultaneously turning it counterclockwise. There are two different sets of manufacturer's instructions for this closure.

One set of the manufacturer's instructions on the closure are (Figure 3):



Figure 3

(This is a pictorial overcap. There is a picture of a closure with an arrow labeled 1 pointing down on the closure in the picture and an arrow labeled 2 on the skirt of the closure in the picture pointing counterclockwise.)

Another example of the instructions for this closure are (Figure 4):



Figure 4

CLOSE TIGHTLY
(arrow clockwise)

TO OPEN
(counterclockwise arrow)
PUSH DOWN & TURN